


PRODUCT-DETAILS

3GAA188429-ADG

(3GAA188429-ADG)



General Information

Product ID	3GAA188429-ADG
ABB Type Designation	M3AA 180MLB 4-8
Catalog Description	(3GAA188429-ADG)

Ordering

ABB Type Designation	M3AA 180MLB 4-8
Invoice Description	M3AA 180MLB 4-8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA188128-ADG

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
YY	--	50 Hz	400 V	22.00 kW	1480 r/min	41.60 A	0.840	90.80 %	142.00 N·m	7.90
Y	--	50 Hz	400 V	4.40 kW	741 r/min	14.40 A	0.520	84.30 %	57.00 N·m	3.80
Temperature Class										--
Default										
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class NA
										Full Load (100%) 84.3 %
										Partial Load (75%) 84.0 %
										Partial Load (50%) 80.7 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										Yes
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Aluminum
Frame Size	180
Bearing	6310-2Z/C3
Bearing NDE	6209-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	177 kg
Gross Weight	187 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

