



## PRODUCT-DETAILS

# 3GAA201034-BEG

## No Description Available

## "No longer for sale" replaced by 3GAA201440-

### General Information

Product ID	3GAA201034-BEG
ABB Type Designation	M3AA 200MLD 2
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M3AA 200MLD 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6312-2Z/C3
Bearing NDE	6210-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides

#### Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	500 V	55.00 kW	2953 r/min	76.00 A	0.890
D	--	60 Hz	575 V	55.00 kW	3560 r/min	65.80 A	0.890

Frame Material	Aluminum
Frame Size	200
Gross Weight	253 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 93.8 % Partial Load (75%) 94.5 % Partial Load (50%) 94.3 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 94.3 % Partial Load (75%) 94.4 % Partial Load (50%) 93.4 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	2
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor

Product Net Weight	251 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA201004-BEC
Replacement Product ID (NEW)	3GAA201440-BEG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	E