

PRODUCT-DETAILS

3GAA201420-AEG

IE2 High Efficiency Aluminum Motors, 37 kW, 500 V (3GAA201420-AEG)



General Information	
Product ID	3GAA201420-AEG
ABB Type Designation	M3AA 200MLB 2
Catalog Description	IE2 High Efficiency Aluminum Motors, 37 kW, 500 V (3GAA201420-AEG)

Ordering	
ABB Type Designation	M3AA 200MLB 2
Invoice Description	M3AA 200MLB 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA201036-AEG
Medium Description	37kW, 2 Poles, Frame Size 200, 3 Phases, 500V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA201420-AEG)

Short Description

37kW, 2P, Frame Size 200, 3PH, 500V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	500 V	37.00 kW	2959 r/min	51.60 A	0.900	93.40 %	119.00 N·m	8.20
D	--	60 Hz	575 V	37.00 kW	3564 r/min	45.30 A	0.890	93.40 %	99.10 N·m	9.20

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U _{in})	500 V
Frequency (f)	50 Hz
Output Power	37 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 93.4 % Partial Load (75%) 93.7 % Partial Load (50%) 92.9 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 93.4 % Partial Load (75%) 93.2 % Partial Load (50%) 91.7 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	E

Mechanical

Frame Material	Aluminum
Frame Size	200
Bearing	6312-2Z/C3
Bearing NDE	6210-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	821 mm
Product Net Height	500 mm
Product Net Width	386 mm
Product Net Weight	225 kg

Gross Weight	235 kg
--------------	--------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

