



PRODUCT-DETAILS

3GAA209419-ADG

IE2 High Efficiency Aluminum Motors, 13/22 kW, 400 V (3GAA209419-ADG)



General Information	
Product ID	3GAA209419-ADG
ABB Type Designation	M3AA 200MLA 4-8
Catalog Description	IE2 High Efficiency Aluminum Motors, 13/22 kW, 400 V (3GAA209419-ADG)

Ordering	
ABB Type Designation	M3AA 200MLA 4-8
Invoice Description	M3AA 200MLA 4-8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA208127-ADG
Medium Description	13/22kW, 4/8 Poles, Frame Size 200, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA209419-ADG)
Short Description	13/22kW, 4/8P, Frame Size 200, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical											
Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
YY	--	50 Hz	400 V	22.00 kW	1480 r/min	41.40 A	0.870	88.00 %	142.00 N·m	6.80	
D	--	50 Hz	400 V	13.00 kW	739 r/min	31.10 A	0.700	86.00 %	168.00 N·m	5.30	
Connection Configuration										D/YY	
Temperature Class Default										--	
Input Voltage (U _{in})										400 V	
Frequency (f)										50 Hz	
Output Power										13/22 kW	
Altitude										1000 m	
Ambient Temperature										40 °C	
IC Class										IC411	
IE Class Data (50 Hz)										IE Class NA Full Load (100%) 86.0 % Partial Load (75%) 87.0 % Partial Load (50%) 85.9 %	
IP Class										IP55	
Insulation Class										ICLF	
Direction of Rotation										Both sides	
Number of Poles (High)										4	
Two Speed Motor										Yes	
Type of Duty										S1	
Voltage Code										D	
Mechanical											
Frame Material										Aluminum	
Frame Size										200	
Bearing										6312-2Z/C3	
Bearing NDE										6210-2Z/C3	
IM Class										IMB3 IM1001	
Terminator Box Location										D-End top	
Dimensions											
Package Level 1 Units										0 pallet (lift)	
Product Net Depth / Length										821 mm	
Product Net Height										500 mm	
Product Net Width										385 mm	
Product Net Weight										218 kg	
Gross Weight										228 kg	
Environmental											

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

