



PRODUCT-DETAILS

3GAA201440-AEG

IE2 High Efficiency Aluminum Motors, 55 kW,
500 V (3GAA201440-AEG)



General Information

Product ID	3GAA201440-AEG
ABB Type Designation	M3AA 200MLD 2
Catalog Description	IE2 High Efficiency Aluminum Motors, 55 kW, 500 V (3GAA201440-AEG)

Ordering

ABB Type Designation	M3AA 200MLD 2
Invoice Description	M3AA 200MLD 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015290
Replaced Product ID (OLD)	3GAA201034-AEG
Medium Description	55kW, 2 Poles, Frame Size 200, 3 Phases, 500V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA201440-AEG)
Short Description	55kW, 2P, Frame Size 200, 3PH, 500V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
D	--	50 Hz	500 V	55.00 kW	2953 r/min	77.20 A	0.890	93.80 %	177.00 N·m	7.80	
D	--	60 Hz	575 V	55.00 kW	3560 r/min	66.80 A	0.890	94.30 %	147.00 N·m	9.00	
Connection Configuration										D	
Temperature Class Default										--	
Input Voltage (U _{in})										500 V	
Frequency (f)										50 Hz	
Output Power										55 kW	
Altitude										1000 m	
Ambient Temperature										40 °C	
IC Class										IC411	
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 93.8 % Partial Load (75%) 94.4 % Partial Load (50%) 94.3 %	
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 94.3 % Partial Load (75%) 94.4 % Partial Load (50%) 93.4 %	
IP Class										IP55	
Insulation Class										ICLF	
Direction of Rotation										Both sides	
Number of Poles (High)										2	
Two Speed Motor										No	
Type of Duty										S1	
Voltage Code										E	

Mechanical

Frame Material	Aluminum
Frame Size	200
Bearing	6312-2Z/C3
Bearing NDE	6210-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	821 mm
Product Net Height	500 mm
Product Net Width	386 mm
Product Net Weight	241 kg
Gross Weight	251 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

