



PRODUCT-DETAILS

3GAA203410-ASG

IE2 High Efficiency Aluminum Motors, 18.5 kW,
400 V (3GAA203410-ASG)



General Information

Product ID	3GAA203410-ASG
ABB Type Designation	M3AA 200MLA 6
Catalog Description	IE2 High Efficiency Aluminum Motors, 18.5 kW, 400 V (3GAA203410-ASG)

Ordering

ABB Type Designation	M3AA 200MLA 6
Invoice Description	M3AA 200MLA 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA2_M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA203031-ASG 3GAA203061-ASA
Medium Description	18.5kW, 6 Poles, Frame Size 200, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA203410-ASG)
Short Description	18.5kW, 6P, Frame Size 200, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
Y	--	50 Hz	400 V	18.50 kW	988 r/min	36.40 A	0.800	91.60 %	178.00 N·m	6.70	
D	--	50 Hz	230 V	18.50 kW	988 r/min	63.70 A	0.800	91.60 %	178.00 N·m	6.70	
Y	--	50 Hz	415 V	18.50 kW	989 r/min	35.90 A	0.780	91.70 %	178.00 N·m	7.00	
Y	--	60 Hz	440 V	18.50 kW	1188 r/min	32.50 A	0.810	92.10 %	148.00 N·m	6.90	
Y	--	60 Hz	460 V	18.50 kW	1190 r/min	31.80 A	0.790	92.20 %	148.00 N·m	7.50	
Connection Configuration										Y	
Temperature Class Default										--	
Input Voltage (U _{in})										400 V	
Frequency (f)										50 Hz	
Output Power										18.5 kW	
Altitude										1000 m	
Ambient Temperature										40 °C	
IC Class										IC411	
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 91.6 % Partial Load (75%) 92.3 % Partial Load (50%) 91.7 %	
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 92.1 % Partial Load (75%) 92.4 % Partial Load (50%) 91.5 %	
IP Class										IP55	
Insulation Class										ICLF	
Direction of Rotation										Both sides	
Number of Poles (High)										6	
Two Speed Motor										No	
Type of Duty										S1	
Voltage Code										S	

Mechanical

Frame Material	Aluminum
Frame Size	200
Bearing	6312-2Z/C3
Bearing NDE	6210-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	821 mm
Product Net Height	532 mm
Product Net Width	386 mm
Product Net Weight	196 kg
Gross Weight	206 kg

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications	
UNSPSC	26101100

Categories	
Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors	

