



PRODUCT-DETAILS

3GAA203410-BSK

IE3 Premium Efficiency Aluminum Motors, 18.5 kW, 400 V (3GAA203410-BSK)



General Information

Product ID	3GAA203410-BSK
ABB Type Designation	M3AA 200MLA 6
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 18.5 kW, 400 V (3GAA203410-BSK)

Ordering

ABB Type Designation	M3AA 200MLA 6
Invoice Description	M3AA 200MLA 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA3 _M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA203051-BSK
Medium Description	18.5kW, 6 Poles, Frame Size 200, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA203410-BSK)
Short Description	18.5kW, 6P, Frame Size 200, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	18.50 kW	990 r/min	37.30 A	0.770	91.70 %	178.00 N·m	7.50
D	--	50 Hz	230 V	18.50 kW	990 r/min	65.20 A	0.770	91.70 %	178.00 N·m	7.50
Y	--	50 Hz	380 V	18.50 kW	989 r/min	37.80 A	0.800	91.70 %	178.00 N·m	7.00
D	--	50 Hz	220 V	18.50 kW	989 r/min	65.60 A	0.800	91.70 %	178.00 N·m	7.00
Y	--	50 Hz	415 V	18.50 kW	991 r/min	37.40 A	0.740	91.70 %	178.00 N·m	7.80
Y	--	60 Hz	460 V	18.50 kW	1191 r/min	32.30 A	0.770	93.30 %	148.00 N·m	8.60

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	18.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 91.7 % Partial Load (75%) 91.9 % Partial Load (50%) 90.9 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 93.3 % Partial Load (75%) 93.2 % Partial Load (50%) 92.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	200
Bearing	6312-2Z/C3
Bearing NDE	6210-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	821 mm
Product Net Height	532 mm
Product Net Width	380 mm
Product Net Weight	218 kg
Gross Weight	228 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

