



PRODUCT-DETAILS

# 3GAA222220-ADK

## IE3 Premium Efficiency Aluminum Motors, 45 kW, 400 V (3GAA222220-ADK)



General Information

Product ID	3GAA222220-ADK
ABB Type Designation	M3AA 225SMB 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 45 kW, 400 V (3GAA222220-ADK)

Ordering

ABB Type Designation	M3AA 225SMB 4
Invoice Description	M3AA 225SMB 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA3 _M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Poland (PL) Finland (FI)
Customs Tariff Number	85015290
Replaced Product ID (OLD)	3GAA222052-ADK
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain
Medium Description	45kW, 4 Poles, Frame Size 225, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA222220-ADK)

Short Description45kW, 4P, Frame Size 225, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	45.00 kW	1482 r/min	47.60 A	0.840	94.20 %	290.00 N·m	8.00
D	--	50 Hz	400 V	45.00 kW	1482 r/min	82.30 A	0.840	94.20 %	290.00 N·m	8.00
Y	--	50 Hz	660 V	45.00 kW	1478 r/min	48.70 A	0.860	94.20 %	290.60 N·m	7.30
D	--	50 Hz	380 V	45.00 kW	1478 r/min	85.00 A	0.860	94.20 %	290.60 N·m	7.30
D	--	50 Hz	415 V	45.00 kW	1483 r/min	81.00 A	0.820	94.20 %	290.00 N·m	8.60
D	--	60 Hz	460 V	45.00 kW	1784 r/min	71.80 A	0.830	95.00 %	241.20 N·m	8.80

Connection Configuration	D
Temperature Class	--
Default	
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	45 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 94.2 % Partial Load (75%) 94.3 % Partial Load (50%) 93.8 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 95.0 % Partial Load (75%) 95.0 % Partial Load (50%) 94.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	225
Bearing	6313-2Z/C3
Bearing NDE	6212-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	880 mm
Product Net Height	553 mm

Product Net Width	418 mm
Product Net Weight	316 kg
Gross Weight	326 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

