




PRODUCT-DETAILS

3GAA223220-BSK

IE3 Premium Efficiency Aluminum Motors, 37 kW, 400 V (3GAA223220-BSK)



General Information

Product ID	3GAA223220-BSK
ABB Type Designation	M3AA 225SMB 6
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 37 kW, 400 V (3GAA223220-BSK)

Ordering

ABB Type Designation	M3AA 225SMB 6
Invoice Description	M3AA 225SMB 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA223054-BSK
Medium Description	37kW, 6 Poles, Frame Size 225, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA223220-BSK)
Short Description	37kW, 6P, Frame Size 225, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	37.00 kW	986 r/min	75.10 A	0.760	93.30 %	357.60 N·m	7.70
D	--	50 Hz	230 V	37.00 kW	986 r/min	130.00 A	0.760	93.30 %	357.60 N·m	7.70
Y	--	50 Hz	380 V	37.00 kW	985 r/min	76.20 A	0.790	93.30 %	358.19 N·m	7.10
D	--	50 Hz	220 V	37.00 kW	985 r/min	132.00 A	0.790	93.30 %	358.19 N·m	7.10
Y	--	50 Hz	415 V	37.00 kW	987 r/min	75.40 A	0.730	93.30 %	357.26 N·m	8.00
Y	--	60 Hz	460 V	37.00 kW	1189 r/min	65.50 A	0.750	94.10 %	2974.00 N·m	8.80

Connection Configuration	Y
Temperature Class	--
Default	
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	37 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 93.3 % Partial Load (75%) 93.4 % Partial Load (50%) 92.7 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 94.1 % Partial Load (75%) 94.1 % Partial Load (50%) 93.2 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	225
Bearing	6313-2Z/C3
Bearing NDE	6212-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	880 mm
Product Net Height	553 mm
Product Net Width	418 mm
Product Net Weight	307 kg
Gross Weight	317 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

