



PRODUCT-DETAILS

3GAA224230-AEG

IE2 High Efficiency Aluminum Motors, 30 kW, 500 V (3GAA224230-AEG)



General Information	
Product ID	3GAA224230-AEG
ABB Type Designation	M3AA 225SMC 8
Catalog Description	IE2 High Efficiency Aluminum Motors, 30 kW, 500 V (3GAA224230-AEG)

Ordering	
ABB Type Designation	M3AA 225SMC 8
Invoice Description	M3AA 225SMC 8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA224033-AEG
Medium Description	30kW, 8 Poles, Frame Size 225, 3 Phases, 500V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GAA224230-AEG)

Short Description

30kW, 8P, Frame Size 225, 3PH, 500V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	500 V	30.00 kW	737 r/min	51.80 A	0.730	91.20 %	388.00 N·m	5.60
D	--	60 Hz	575 V	30.00 kW	889 r/min	45.10 A	0.720	91.60 %	322.00 N·m	6.40

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U _{in})	500 V
Frequency (f)	50 Hz
Output Power	30 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 91.2 % Partial Load (75%) 92.3 % Partial Load (50%) 92.1 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 91.6 % Partial Load (75%) 92.0 % Partial Load (50%) 91.2 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	8
Two Speed Motor	No
Type of Duty	S1
Voltage Code	E

Mechanical

Frame Material	Aluminum
Frame Size	225
Bearing	6313-2Z/C3
Bearing NDE	6212-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	850 mm
Product Net Height	547 mm
Product Net Width	425 mm
Product Net Weight	300 kg

Gross Weight310 kg

Environmental

WEEE Category4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

