



PRODUCT-DETAILS

3GAA252210-BDK

IE3 Premium Efficiency Aluminum Motors, 55 kW, 400 V (3GAA252210-BDK)



General Information

Product ID	3GAA252210-BDK
ABB Type Designation	M3AA 250SMA 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 55 kW, 400 V (3GAA252210-BDK)

Ordering

ABB Type Designation	M3AA 250SMA 4
Invoice Description	M3AA 250SMA 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA3 _M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Poland (PL) Finland (FI)
Customs Tariff Number	85015290
Replaced Product ID (OLD)	3GAA252051-BDK
Stocked At (Warehouses)	Menden, Germany Sant Quirze del Vallés - BCN, Spain
Medium Description	55kW, 4 Poles, Frame Size 250, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA252210-BDK)

Short Description55kW, 4P, Frame Size 250, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	55.00 kW	1485 r/min	56.70 A	0.850	94.60 %	353.00 N·m	7.90
D	--	50 Hz	400 V	55.00 kW	1485 r/min	97.80 A	0.850	94.60 %	353.00 N·m	7.90
Y	--	50 Hz	660 V	55.00 kW	1482 r/min	58.80 A	0.860	94.60 %	353.00 N·m	7.20
D	--	50 Hz	380 V	55.00 kW	1482 r/min	102.00 A	0.860	94.60 %	353.00 N·m	7.20
D	--	50 Hz	415 V	55.00 kW	1486 r/min	95.20 A	0.840	94.60 %	353.00 N·m	8.50
D	--	60 Hz	460 V	55.00 kW	1787 r/min	85.80 A	0.840	95.70 %	293.00 N·m	9.10

Connection Configuration	D
Temperature Class	--
Default	
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	55 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 94.6 % Partial Load (75%) 94.9 % Partial Load (50%) 94.6 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 95.7 % Partial Load (75%) 95.8 % Partial Load (50%) 95.2 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	250
Bearing	6315-2Z/C3
Bearing NDE	6213-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	884 mm
Product Net Height	601 mm

Product Net Width	473 mm
Product Net Weight	376 kg
Gross Weight	386 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

