


PRODUCT-DETAILS

3GAA259219-ADG

(3GAA259219-ADG)



General Information

Product ID	3GAA259219-ADG
ABB Type Designation	M3AA 250SMA 4-8
Catalog Description	(3GAA259219-ADG)

Ordering

ABB Type Designation	M3AA 250SMA 4-8
Invoice Description	M3AA 250SMA 4-8
Product Name	3-Phase squirrel cage motor
Product Type	3AA2__M3AA_IE2_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015290
Replaced Product ID (OLD)	3GAA258113-ADG

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
YY	--	50 Hz	400 V	55.00 kW	1486 r/min	98.30 A	0.880	91.70 %	354.00 N·m	7.50
D	--	50 Hz	400 V	30.00 kW	744 r/min	75.30 A	0.640	89.80 %	385.00 N·m	6.30

Temperature Class	--
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class NA Full Load (100%) 89.8 % Partial Load (75%) 89.9 % Partial Load (50%) 88.4 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	Yes
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Aluminum
Frame Size	250
Bearing	6315-2Z/C3
Bearing NDE	6213-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Weight	367 kg
Gross Weight	377 kg

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE2 High Efficiency Aluminum Motors

