



PRODUCT-DETAILS

3GAA252061-ASA

No Description Available

"No longer for sale" replaced by 3GAA252210-

General Information	
Product ID	3GAA252061-ASA
ABB Type Designation	M1AA 250SMA 4
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M1AA 250SMA 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6315/C3
Bearing NDE	6313-2Z/C3
Country of Origin	Turkiye (TR)
Customs Tariff Number	85015290
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	55.00 kW	1470 r/min	173.00 A	0.860
Y	--	50 Hz	400 V	55.00 kW	1470 r/min	100.00 A	0.860
Y	--	60 Hz	460 V	55.00 kW	1770 r/min	87.00 A	0.850

Frame Material	Aluminum
Frame Size	250
Gross Weight	0 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 92.1 % Partial Load (75%) 92.0 % Partial Load (50%) 90.9 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 93.4 % Partial Load (75%) 93.3 % Partial Load (50%) 92.2 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No

Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	0 kg
Product Type	1AA1__M1AA_IE1_AA
Quote Only	No
Replacement Product ID (NEW)	3GAA252210-ASG
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)