



PRODUCT-DETAILS

3GAA253031-ASG

No Description Available

"No longer for sale" replaced by 3GAA253210-

General Information

Product ID	3GAA253031-ASG
ABB Type Designation	M3AA 250SMA 6
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M3AA 250SMA 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6315-2Z/C3
Bearing NDE	6213-2Z/C3
Country of Origin	Sweden (SE)
Customs Tariff Number	85015230
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	230 V	37.00 kW	989 r/min	121.00 A	0.820
Y	--	50 Hz	400 V	37.00 kW	989 r/min	69.90 A	0.820
Y	--	50 Hz	415 V	37.00 kW	990 r/min	69.10 A	0.800
Y	--	60 Hz	460 V	37.00 kW	1191 r/min	61.20 A	0.810

Frame Material	Aluminum
Frame Size	250
Gross Weight	294 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 93.1 % Partial Load (75%) 93.7 % Partial Load (50%) 93.2 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 93.6 % Partial Load (75%) 93.8 % Partial Load (50%) 93.1 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Moment of Inertia	0.00000 kg/m³
Number of Poles (High)	6

Package Level 1 Units	0 pallet (lift)
Product Name	3-Phase squirrel cage motor
Product Net Weight	294 kg
Product Type	3AA2_M3AA_IE2_AA
Quote Only	No
Replaced Product ID (OLD)	3GAA253001-ASC
Replacement Product ID (NEW)	3GAA253210-ASG
Selling Unit of Measure	piece
Service Factor	0.00
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S