

PRODUCT-DETAILS

3GAA253210-BEK

IE3 Premium Efficiency Aluminum Motors, 37 kW, 500 V (3GAA253210-BEK)



General Information	
Product ID	3GAA253210-BEK
ABB Type Designation	M3AA 250SMA 6
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 37 kW, 500 V (3GAA253210-BEK)

Ordering	
ABB Type Designation	M3AA 250SMA 6
Invoice Description	M3AA 250SMA 6
Product Name	3-Phase squirrel cage motor
Product Type	3AA3 _M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015230
Replaced Product ID (OLD)	3GAA253051-BEK
Medium Description	37kW, 6 Poles, Frame Size 250, 3 Phases, 500V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAA253210-BEK)

Short Description

37kW, 6P, Frame Size 250, 3PH, 500V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	500 V	37.00 kW	991 r/min	54.80 A	0.830	93.30 %	356.00 N·m	7.50
D	--	60 Hz	575 V	37.00 kW	1192 r/min	48.10 A	0.820	94.50 %	296.00 N·m	8.40

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U _{in})	500 V
Frequency (f)	50 Hz
Output Power	37 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 93.3 % Partial Load (75%) 93.9 % Partial Load (50%) 93.7 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 94.5 % Partial Load (75%) 94.7 % Partial Load (50%) 94.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	E

Mechanical

Frame Material	Aluminum
Frame Size	250
Bearing	6315-2Z/C3
Bearing NDE	6213-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 pallet (lift)
Product Net Depth / Length	884 mm
Product Net Height	601 mm
Product Net Width	473 mm
Product Net Weight	367 kg

Gross Weight	377 kg
--------------	--------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

