



PRODUCT-DETAILS

# 3GBA071211-CDB

## No Description Available

General Information										
Product ID	3GBA071211-CDB									
ABB Type Designation	M2BA 71MA 2									
Catalog Description	No Description Available									
Additional Information										
ABB Type Designation	M2BA 71MA 2									
Altitude	1000 m									
Ambient Temperature	40 °C									
Bearing	6203-2Z/C3									
Bearing NDE	6202-2Z/C3									
Country of Origin	India (IN) China (CN)									
Customs Tariff Number	85015100									
Direction of Rotation	Both sides									
Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	0.37 kW	2660 r/min	0.55 A	0.800	69.20 %	1.32 N·m	3.90
D	--	50 Hz	400 V	0.37 kW	2660 r/min	0.96 A	0.800	69.20 %	1.32 N·m	3.90
D	--	60 Hz	460 V	0.37 kW	3325 r/min	0.73 A	0.820	76.70 %	1.06 N·m	5.80
Frame Size	71									
Gross Weight	11.5 kg									
IC Class	IC411									
IM Class	IMB14 IM3601									
Insulation Class	ICLF									
IP Class	IP55									
Lubrication	For life									
Made To Order	No									
Minimum Order Quantity	1 piece									
Number of Poles (High)	2									
Package Level 1 Units	0 carton									
Product Name	3-Phase squirrel cage motor									
Product Net Weight	11 kg									
Product Type	2BA2_M2BA_IE2_CI									
Quote Only	No									
Selling Unit of Measure	piece									

Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)