



PRODUCT-DETAILS

3GBA071001-ASB

No Description Available

| General Information | |
|----------------------|--------------------------|
| Product ID | 3GBA071001-ASB |
| ABB Type Designation | M2BA 71 A2 |
| Catalog Description | No Description Available |

| Additional Information | |
|------------------------|--------------------------|
| ABB Type Designation | M2BA 71 A2 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6202-2Z/C3 |
| Bearing NDE | 6202-2Z/C3 |
| Country of Origin | India (IN) China (CN) |
| Customs Tariff Number | 85015100 |
| Direction of Rotation | Both sides |
| Electrical Data | |

| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor | Torque |
|------|------------|-------|-----------|---------|------------|---------|--------------|----------|
| Y | -- | 50 Hz | 380-420 V | 0.37 kW | 2735 r/min | 0.95 A | 0.830 | 1.29 N·m |
| D | -- | 50 Hz | 220-240 V | 0.37 kW | 2735 r/min | 1.64 A | 0.830 | 1.29 N·m |
| Y | -- | 60 Hz | 440-480 V | 0.45 kW | 3280 r/min | 0.82 A | 0.830 | 1.29 N·m |

| | |
|------------------------|-----------------------------|
| Frame Size | 71 |
| Gross Weight | 10.26 kg |
| IC Class | IC411 |
| IM Class | IMB3 IM1001 |
| Insulation Class | ICLF |
| IP Class | IP55 |
| Lubrication | For life |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Number of Poles (High) | 2 |
| Package Level 1 Units | 0 carton |
| Product Name | 3-Phase squirrel cage motor |
| Product Net Weight | 10 kg |

| | |
|------------------------------|--|
| Product Type | 2BA2__M2BA_IE2_CI |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Direct Online |
| Temperature Class Default | -- |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | S |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |