



PRODUCT-DETAILS

# 3GBA072211-ASB

## No Description Available

### General Information

Product ID	3GBA072211-ASB
ABB Type Designation	M2BA 71MA 4
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M2BA 71MA 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
Country of Origin	India (IN) China (CN) Poland (PL)
Customs Tariff Number	85015100

#### Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.25 kW	1365 r/min	0.64 A	0.810	68.50 %	1.74 N·m	3.50
D	--	50 Hz	230 V	0.25 kW	1365 r/min	1.12 A	0.810	68.50 %	1.74 N·m	3.50
Y	--	60 Hz	460 V	0.25 kW	1705 r/min	0.56 A	0.750	73.50 %	1.42 N·m	4.30

Frame Size	71
Gross Weight	13 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 68.5 % Partial Load (75%) 70.9 % Partial Load (50%) 69.8 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 73.5 % Partial Load (75%) 73.4 % Partial Load (50%) 70.6 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	10 kg
Product Type	2BA2_M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class	--
Default	
Terminator Box Location	Top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)