



PRODUCT-DETAILS

3GBA073211-ADBCN

No Description Available

General Information	
Product ID	3GBA073211-ADBCN
ABB Type Designation	M2BA 71MA 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 71MA 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque	IS/IN
D	--	50 Hz	380 V	0.18 kW	870 r/min	0.58 A	0.750	1.97 N-m	3.00
Y	--	50 Hz	660 V	0.18 kW	870 r/min	0.34 A	0.750	1.97 N-m	3.00
D	--	50 Hz	400 V	0.18 kW	900 r/min	0.57 A	0.710	1.91 N-m	3.10

Frame Size	71
Gross Weight	10 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	10 kg

Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)