



PRODUCT-DETAILS

3GBA073211-HSB

No Description Available

General Information	
Product ID	3GBA073211-HSB
ABB Type Designation	M2BA 71MA 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 71MA 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015100
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.18 kW	900 r/min	0.57 A	0.710	63.70 %	1.91 N·m	3.10
D	--	50 Hz	230 V	0.18 kW	900 r/min	0.99 A	0.710	63.70 %	1.91 N·m	3.10
Y	--	60 Hz	460 V	0.18 kW	1120 r/min	0.52 A	0.620	69.00 %	1.53 N·m	3.80

Frame Size	71
Gross Weight	13 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 63.7 % Partial Load (75%) 63.8 % Partial Load (50%) 59.0 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 69.0 % Partial Load (75%) 68.1 % Partial Load (50%) 63.5 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life

Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Package Level 1 Units	0 carton
Pre Modified Motor	3GBA073211-ASB
Product ID	
Product Name	3-Phase squirrel cage motor
Product Net Weight	10 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class	--
Default	
Terminator Box Location	Top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)