



PRODUCT-DETAILS

# 3GBA073212-BSBCN

## No Description Available

General Information	
Product ID	3GBA073212-BSBCN
ABB Type Designation	M2BA 71MB 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 71MB 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	0.25 kW	875 r/min	1.35 A	0.730	66.50 %	2.70 N-m	3.30
Y	--	50 Hz	380 V	0.25 kW	875 r/min	0.78 A	0.730	66.50 %	2.70 N-m	3.30
D	--	50 Hz	230 V	0.25 kW	895 r/min	1.33 A	0.690	67.20 %	2.60 N-m	3.40

Frame Size	71
Gross Weight	12 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	12 kg

Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)