



PRODUCT-DETAILS

3GBA073310-BSEIN  
M2BAX 71MA 6

General Information																																												
Product ID								3GBA073310-BSEIN																																				
ABB Type Designation								M2BAX 71MA 6																																				
Catalog Description								M2BAX 71MA 6																																				
Additional Information																																												
ABB Type Designation								M2BAX 71MA 6																																				
Altitude								1000 m																																				
Ambient Temperature								50 °C																																				
Bearing								6203-2Z/C3																																				
Bearing NDE								6202-2Z/C3																																				
Country of Origin								India (IN)																																				
Customs Tariff Number								85015100																																				
Direction of Rotation								Both sides																																				
Electrical Data																																												
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th><th>Efficiency</th><th>Torque</th><th>IS/IN</th></tr><tr><td>Y</td><td>--</td><td>50 Hz</td><td>400 V</td><td>0.18 kW</td><td>882 r/min</td><td>0.64 A</td><td>0.720</td><td>56.00 %</td><td>1.90 N·m</td><td>3.40</td></tr><tr><td>Y</td><td>--</td><td>50 Hz</td><td>415 V</td><td>0.18 kW</td><td>900 r/min</td><td>0.63 A</td><td>0.710</td><td>56.00 %</td><td>1.90 N·m</td><td>3.50</td></tr></table>												Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	Y	--	50 Hz	400 V	0.18 kW	882 r/min	0.64 A	0.720	56.00 %	1.90 N·m	3.40	Y	--	50 Hz	415 V	0.18 kW	900 r/min	0.63 A	0.710	56.00 %	1.90 N·m	3.50
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN																																		
Y	--	50 Hz	400 V	0.18 kW	882 r/min	0.64 A	0.720	56.00 %	1.90 N·m	3.40																																		
Y	--	50 Hz	415 V	0.18 kW	900 r/min	0.63 A	0.710	56.00 %	1.90 N·m	3.50																																		
Frame Material								Cast Iron																																				
Frame Size								71																																				
Gross Weight								12 kg																																				
IC Class								IC411																																				
IE Class Data (50 Hz)								IE Class IE1 Full Load (100%) 56.0 % Partial Load (75%) 54.2 % Partial Load (50%) 47.0 %																																				
IM Class								IMB5 IM3001																																				
Insulation Class								ICLF																																				
Invoice Description								M2BAX 71MA 6																																				
IP Class								IP55																																				
Made To Order								No																																				
Minimum Order Quantity								1 piece																																				
Number of Poles (High)								6																																				
Order Multiple								1 piece																																				

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	9 kg
Product Type	IBA1__M2BAX_IE1_CI
Quote Only	No
Selling Unit of Measure	piece
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S