



PRODUCT-DETAILS

3GBA073211-CFB

No Description Available

| General Information | |
|----------------------|--------------------------|
| Product ID | 3GBA073211-CFB |
| ABB Type Designation | M2BA 71MA 6 |
| Catalog Description | No Description Available |

| Additional Information | |
|------------------------|--------------------------|
| ABB Type Designation | M2BA 71MA 6 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6203-2Z/C3 |
| Bearing NDE | 6202-2Z/C3 |
| Country of Origin | India (IN) China (CN) |
| Customs Tariff Number | 85015100 |
| Direction of Rotation | Both sides |
| Electrical Data | |

| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor | Efficiency | Torque | IS/IN |
|------|------------|-------|---------|---------|------------|---------|--------------|------------|----------|-------|
| Y | -- | 50 Hz | 500 V | 0.18 kW | 900 r/min | 0.45 A | 0.710 | 63.70 % | 1.91 N·m | 3.10 |
| Y | -- | 60 Hz | 575 V | 0.18 kW | 1120 r/min | 0.41 A | 0.620 | 69.00 % | 1.53 N·m | 4.00 |

| | |
|------------------------|-----------------------------|
| Frame Size | 71 |
| Gross Weight | 10.5 kg |
| IC Class | IC411 |
| IM Class | IMB14 IM3601 |
| Insulation Class | ICLF |
| IP Class | IP55 |
| Lubrication | For life |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Number of Poles (High) | 6 |
| Package Level 1 Units | 0 carton |
| Product Name | 3-Phase squirrel cage motor |
| Product Net Weight | 10 kg |
| Product Type | 2BA2_M2BA_IE2_CI |

| | |
|------------------------------|--|
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Direct Online |
| Temperature Class Default | -- |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | F |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |