


PRODUCT-DETAILS

3GBA073310-BST
M2BAX 71MA 6



General Information	
Product ID	3GBA073310-BST
ABB Type Designation	M2BAX 71MA 6
Catalog Description	M2BAX 71MA 6

Ordering	
ABB Type Designation	M2BAX 71MA 6
Invoice Description	M2BAX 71MA 6
Product Name	3-Phase squirrel cage motor
Product Type	EBA1_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.18 kW	910 r/min	0.63 A	0.710	45.50 %	1.87 N·m	3.30
D	--	50 Hz	230 V	0.18 kW	910 r/min	1.09 A	0.710	45.50 %	1.87 N·m	3.30
Y	--	50 Hz	380 V	0.18 kW	890 r/min	0.63 A	0.760	45.50 %	1.87 N·m	3.10
D	--	50 Hz	220 V	0.18 kW	890 r/min	1.09 A	0.760	45.50 %	1.87 N·m	3.10
Y	--	60 Hz	440 V	0.18 kW	1109 r/min	0.52 A	0.730	52.50 %	1.50 N·m	4.20
Y	--	60 Hz	460 V	0.18 kW	1117 r/min	0.59 A	0.640	52.50 %	1.49 N·m	3.80
Temperature Class										--
Default										
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE1 Full Load (100%) 45.5 % Partial Load (75%) 39.9 % Partial Load (50%) 30.2 %
IE Class Data (60 Hz)										IE Class IE1 Full Load (100%) 52.5 % Partial Load (75%) 45.5 % Partial Load (50%) 36.3 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Cast Iron
Frame Size	71
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	9 kg
Gross Weight	12 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE1 Standard Efficiency Cast Iron Motors

