


PRODUCT-DETAILS

3GBA081320-BDT

M2BAX 80MB 2



General Information	
Product ID	3GBA081320-BDT
ABB Type Designation	M2BAX 80MB 2
Catalog Description	M2BAX 80MB 2

Ordering	
ABB Type Designation	M2BAX 80MB 2
Invoice Description	M2BAX 80MB 2
Product Name	3-Phase squirrel cage motor
Product Type	EBA1_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	1.10 kW	2840 r/min	1.41 A	0.830	75.00 %	3.67 N·m	6.00
D	--	50 Hz	400 V	1.10 kW	2840 r/min	2.44 A	0.830	75.00 %	3.67 N·m	6.00
Y	--	50 Hz	660 V	1.10 kW	2819 r/min	1.44 A	0.860	75.00 %	3.67 N·m	5.50
D	--	50 Hz	380 V	1.10 kW	2821 r/min	2.49 A	0.860	75.00 %	3.67 N·m	5.50
D	--	60 Hz	440 V	1.10 kW	3445 r/min	2.18 A	0.830	78.50 %	3.04 N·m	6.80
D	--	60 Hz	460 V	1.10 kW	3460 r/min	2.16 A	0.800	78.50 %	3.03 N·m	7.20
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE1 Full Load (100%) 75.0 % Partial Load (75%) 74.9 % Partial Load (50%) 72.6 %
IE Class Data (60 Hz)										IE Class IE1 Full Load (100%) 78.5 % Partial Load (75%) 77.1 % Partial Load (50%) 73.6 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical										
Frame Material										Cast Iron
Frame Size										80
Bearing										6204-2Z/C3
Bearing NDE										6203-2Z/C3
IM Class										IMB5 IM3001
Terminator Box Location										D-End top

Dimensions										
Package Level 1 Units										0 carton
Product Net Weight										15 kg
Gross Weight										18 kg

Environmental										
WEEE Category										5. Small Equipment (No External Dimension More Than 50 cm)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE1 Standard Efficiency Cast Iron Motors

