



PRODUCT-DETAILS

3GBA081310-BSCCNAC
M2BAX 80MA2

General Information

| | |
|----------------------|--------------------|
| Product ID | 3GBA081310-BSCCNAC |
| ABB Type Designation | M2BAX 80MA 2 |
| Catalog Description | M2BAX 80MA2 |

Additional Information

| | |
|-----------------------|--------------|
| ABB Type Designation | M2BAX 80MA 2 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6204-2RS/C3 |
| Bearing NDE | 6203-2RS/C3 |
| Country of Origin | China (CN) |
| Customs Tariff Number | 85015100 |
| Direction of Rotation | Both sides |

Electrical Data

| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor | Efficiency | Torque | IS/IN |
|------|------------|-------|---------|---------|------------|---------|--------------|------------|----------|-------|
| Y | -- | 50 Hz | 380 V | 0.75 kW | 2797 r/min | 1.71 A | 0.860 | 77.40 % | 2.51 N·m | 5.30 |
| D | -- | 50 Hz | 220 V | 0.75 kW | 2797 r/min | 2.96 A | 0.860 | 77.40 % | 2.51 N·m | 5.30 |
| Y | -- | 50 Hz | 400 V | 0.75 kW | 2830 r/min | 1.69 A | 0.830 | 77.40 % | 2.51 N·m | 5.70 |

| | |
|------------------------|---|
| Frame Size | 80 |
| Gross Weight | 13 kg |
| IC Class | IC411 |
| IE Class Data (50 Hz) | IE Class IE2 Full Load (100%) 77.4 % Partial Load (75%) 76.5 % Partial Load (50%) 76.2 % |
| IM Class | IMB5 IM3001 |
| Insulation Class | ICLF |
| Invoice Description | M2BAX 80MA2 |
| IP Class | IP55 |
| Lubrication | For life |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Number of Poles (High) | 2 |
| Order Multiple | 1 piece |
| Package Level 1 Units | 0 carton |
| Product Name | 3-Phase squirrel cage motor |

| | |
|------------------------------|--|
| Product Net Weight | 13 kg |
| Product Type | CBA2_M2BAX_CI |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Starting of Motor | Direct Online |
| Stocked At (Warehouses) | Shanghai, China Guangzhou, China |
| Temperature Class Default | -- |
| Temperature Rise | 80 K |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | S |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |