




PRODUCT-DETAILS

3GBA081330-BSD

IE3 Premium Efficiency Cast Iron Motors, 0.75 kW, 400 V (3GBA081330-BSD)



General Information	
Product ID	3GBA081330-BSD
ABB Type Designation	M2BAX 80MC 2
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 0.75 kW, 400 V (3GBA081330-BSD)

Ordering	
ABB Type Designation	M2BAX 80MC 2
Invoice Description	M2BAX 80MC 2
Product Name	3-Phase squirrel cage motor
Product Type	EBA3__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Menden, Germany Shanghai, China
Medium Description	0.75kW, 2 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GBA081330-BSD)
Short Description	0.75kW, 2P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.75 kW	2891 r/min	1.66 A	0.800	80.70 %	2.49 N·m	7.50
D	--	50 Hz	230 V	0.75 kW	2890 r/min	2.85 A	0.810	80.70 %	2.49 N·m	7.50
Y	--	50 Hz	380 V	0.75 kW	2875 r/min	1.68 A	0.840	80.70 %	2.53 N·m	7.00
D	--	50 Hz	220 V	0.75 kW	2876 r/min	2.90 A	0.840	80.70 %	2.50 N·m	7.00

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U <sub>in</sub> )	400 V
Frequency (f)	50 Hz
Output Power	0.75 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 80.7 % Partial Load (75%) 81.0 % Partial Load (50%) 78.9 %
IE Class Data (60 Hz)	IE Class IE3 Full Load (100%) 77.0 % Partial Load (75%) 75.6 % Partial Load (50%) 71.0 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Cast Iron
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	309 mm
Product Net Height	192 mm

Product Net Width	154 mm
Product Net Weight	16 kg
Gross Weight	19 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

