


PRODUCT-DETAILS

3GBA081320-BST

No Description Available



General Information	
Product ID	3GBA081320-BST
ABB Type Designation	M2BAX 80MB 2
Catalog Description	No Description Available

Ordering	
ABB Type Designation	M2BAX 80MB 2
Product Name	3-Phase squirrel cage motor
Product Type	EBA1_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.10 kW	2845 r/min	2.44 A	0.830	75.00 %	3.67 N·m	6.20
D	--	50 Hz	230 V	1.10 kW	2845 r/min	4.23 A	0.830	75.00 %	3.67 N·m	6.20
Y	--	50 Hz	380 V	1.10 kW	2819 r/min	2.50 A	0.860	75.00 %	3.67 N·m	5.60
D	--	50 Hz	220 V	1.10 kW	2819 r/min	4.33 A	0.860	75.00 %	3.67 N·m	5.60
Y	--	60 Hz	440 V	1.10 kW	3445 r/min	2.18 A	0.830	78.50 %	3.00 N·m	6.90
Y	--	60 Hz	460 V	1.10 kW	3460 r/min	2.16 A	0.800	78.50 %	2.99 N·m	7.30
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class NA Full Load (100%) 75.0 % Partial Load (75%) 74.6 % Partial Load (50%) 72.5 %
IE Class Data (60 Hz)										IE Class NA Full Load (100%) 78.5 % Partial Load (75%) 77.0 % Partial Load (50%) 73.5 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	15 kg
Gross Weight	18 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC

26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE1 Standard Efficiency Cast Iron Motors

