

PRODUCT-DETAILS

# 3GBA081330-ASKCN

## (3GBA081330-ASKCN)



General Information	
Product ID	3GBA081330-ASKCN
ABB Type Designation	M2BAF 80MC 2
Catalog Description	(3GBA081330-ASKCN)

Ordering	
ABB Type Designation	M2BAF 80MC 2
Invoice Description	M2BAF 80MC 2
Product Name	3-Phase squirrel cage motor
Product Type	CBF3__M2BAF_IE3_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Shanghai, China Guangzhou, China China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	380 V	0.75 kW	2875 r/min	1.68 A	0.840	80.70 %	2.53 N·m	7.00
D	--	50 Hz	220 V	0.75 kW	2876 r/min	2.90 A	0.840	80.70 %	2.50 N·m	7.00

Temperature Class	--
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 80.7 % Partial Load (75%) 81.5 % Partial Load (50%) 80.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	2
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Cast Iron
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	16 kg
Gross Weight	19 kg

Classifications

UNSPSC	26101100
--------	----------

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

