

PRODUCT-DETAILS

3GBA081410-ASN

IE4 Super Premium Efficiency Cast Iron Motors, 1.1 kW, 400 V (3GBA081410-ASN)



General Information	
Product ID	3GBA081410-ASN
ABB Type Designation	M2BAX 80MLA 2
Catalog Description	IE4 Super Premium Efficiency Cast Iron Motors, 1.1 kW, 400 V (3GBA081410-ASN)

Ordering	
ABB Type Designation	M2BAX 80MLA 2
Invoice Description	M2BAX 80MLA 2
Product Name	3-Phase squirrel cage motor
Product Type	EBA4__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany
Medium Description	1.1kW, 2 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GBA081410-ASN)
Short Description	1.1kW, 2P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
Y	--	50 Hz	400 V	1.10 kW	2884 r/min	2.22 A	0.840	85.20 %	3.65 N·m	8.00	
D	--	50 Hz	230 V	1.10 kW	2884 r/min	3.86 A	0.840	85.20 %	3.65 N·m	8.00	
Y	--	50 Hz	380 V	1.10 kW	2866 r/min	2.28 A	0.860	85.20 %	3.67 N·m	7.50	
D	--	50 Hz	220 V	1.10 kW	2866 r/min	3.94 A	0.860	85.20 %	3.67 N·m	7.50	
Connection Configuration										Y	
Temperature Class Default										--	
Input Voltage (U _{in})										400 V	
Frequency (f)										50 Hz	
Output Power										1.1 kW	
Altitude										1000 m	
Ambient Temperature										40 °C	
IC Class										IC411	
IE Class Data (50 Hz)										IE Class IE4 Full Load (100%) 85.2 % Partial Load (75%) 86.1 % Partial Load (50%) 85.2 %	
IP Class										IP55	
Insulation Class										ICLF	
Direction of Rotation										Both sides	
Number of Poles (High)										2	
Two Speed Motor										No	
Type of Duty										S1	
Voltage Code										S	

Mechanical

Frame Material	Cast Iron
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	337 mm
Product Net Height	192 mm
Product Net Width	154 mm
Product Net Weight	20 kg
Gross Weight	23 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE4 Super Premium Efficiency Cast Iron Motors

