



PRODUCT-DETAILS

3GBA082310-HSVCN

No Description Available

General Information

Product ID	3GBA082310-HSVCN
ABB Type Designation	M2BAK80MA4
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M2BAK80MA4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6204-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	0.55 kW	1430 r/min	2.32 A	0.740	82.10 %	3.67 N·m	17.44
Y	--	50 Hz	380 V	0.55 kW	1430 r/min	1.35 A	0.740	82.10 %	3.67 N·m	10.08

Frame Material	Cast Iron
Frame Size	80
Gross Weight	24 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 82.1 % Partial Load (75%) 84.0 % Partial Load (50%) 82.1 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	24 kg
Product Type	CBK4_M2BAK_IE4_CI
Quote Only	No

Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S