



PRODUCT-DETAILS

# 3GBA082214-JSBCN

## No Description Available

General Information	
Product ID	3GBA082214-JSBCN
ABB Type Designation	M2BA 80MD 4
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 80MD 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	0.75 kW	1420 r/min	3.19 A	0.760	80.70 %	5.00 N·m	5.00
Y	--	50 Hz	380 V	0.75 kW	1420 r/min	1.85 A	0.760	80.70 %	5.00 N·m	5.00
D	--	50 Hz	230 V	0.75 kW	1430 r/min	3.10 A	0.730	81.00 %	5.00 N·m	5.30

Frame Size	80
Gross Weight	17 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 81.0 % Partial Load (75%) 80.7 % Partial Load (50%) 77.3 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 82.6 %
IM Class	IMB34 IM2101
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life

Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	17 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)