



PRODUCT-DETAILS

3GBA082410-ASDCNAB
M2BAX 80MLA

General Information	
Product ID	3GBA082410-ASDCNAB
ABB Type Designation	M2BAX 80MLA 4
Catalog Description	M2BAX 80MLA

Additional Information	
ABB Type Designation	M2BAX 80MLA 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6204-2RS/C3
Bearing NDE	6203-2RS/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	380 V	0.75 kW	1407 r/min	1.75 A	0.790	82.50 %	4.97 N·m	7.00
D	--	50 Hz	220 V	0.75 kW	1407 r/min	3.02 A	0.790	82.50 %	4.97 N·m	5.80
Y	--	60 Hz	460 V	0.75 kW	1730 r/min	1.48 A	0.760	83.50 %	4.97 N·m	5.81

Frame Size	80
Gross Weight	24 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 82.5 % Partial Load (75%) 82.3 % Partial Load (50%) 80.3 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M2BAX 80MLA
IP Class	IP55
Lubrication	For life
Made To Order	No

Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	24 kg
Product Type	CBA3__M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)