



PRODUCT-DETAILS

3GBA083310-ASCCN  
(3GBA083310-ASCCN)



General Information	
Product ID	3GBA083310-ASCCN
ABB Type Designation	M2BAX 80MA 6
Catalog Description	(3GBA083310-ASCCN)

Ordering	
ABB Type Designation	M2BAX 80MA 6
Invoice Description	M2BAX 80MA 6
Product Name	3-Phase squirrel cage motor
Product Type	CBA2__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Shanghai, China Guangzhou, China China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.37 kW	919 r/min	1.12 A	0.720	67.60 %	3.84 N·m	4.20
D	--	50 Hz	230 V	0.37 kW	919 r/min	1.94 A	0.720	67.60 %	3.84 N·m	4.20
Y	--	50 Hz	380 V	0.37 kW	906 r/min	1.11 A	0.770	67.60 %	3.84 N·m	4.00
D	--	50 Hz	220 V	0.37 kW	906 r/min	1.92 A	0.770	67.60 %	3.84 N·m	4.00
Y	--	60 Hz	440 V	0.37 kW	1121 r/min	0.98 A	0.720	64.00 %	3.10 N·m	4.90
Y	--	60 Hz	460 V	0.37 kW	1128 r/min	1.09 A	0.640	64.00 %	3.09 N·m	4.60

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 67.6 % Partial Load (75%) 65.5 % Partial Load (50%) 60.1 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 64.0 % Partial Load (75%) 60.3 % Partial Load (50%) 53.0 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Frame Material	Cast Iron
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6204-2Z/C3
Lubrication	For life
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Package Level 1 Units	0 carton
Product Net Weight	14 kg
Gross Weight	17 kg

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

**Classifications**

Standards	IEC 60034-1
UNSPSC	26101100

**Categories**

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

