



PRODUCT-DETAILS

3GBA083310-HSVCN

No Description Available

General Information											
Product ID	3GBA083310-HSVCN										
ABB Type Designation	M2BAK80MA6										
Catalog Description	No Description Available										
Additional Information											
ABB Type Designation	M2BAK80MA6										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6204-2Z/C3										
Bearing NDE	6204-2Z/C3										
Country of Origin	China (CN)										
Customs Tariff Number	85015100										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	D	--	50 Hz	220 V	0.37 kW	935 r/min	1.83 A	0.660	77.50 %	3.78 N·m	12.45
	Y	--	50 Hz	380 V	0.37 kW	935 r/min	1.06 A	0.660	77.50 %	3.78 N·m	7.21
Frame Material	Cast Iron										
Frame Size	80										
Gross Weight	23 kg										
IC Class	IC411										
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 77.5 % Partial Load (75%) 78.7 % Partial Load (50%) 77.5 %										
IM Class	IMB35 IM2001										
Insulation Class	ICLF										
IP Class	IP55										
Made To Order	No										
Minimum Order Quantity	1 piece										
Number of Poles (High)	6										
Order Multiple	1 piece										
Product Name	3-Phase squirrel cage motor										

Product Net Weight	23 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S