




PRODUCT-DETAILS

3GBA083320-ADT
M2BAX 80MB 6



General Information	
Product ID	3GBA083320-ADT
ABB Type Designation	M2BAX 80MB 6
Catalog Description	M2BAX 80MB 6

Ordering	
ABB Type Designation	M2BAX 80MB 6
Invoice Description	M2BAX 80MB 6
Product Name	3-Phase squirrel cage motor
Product Type	EBA1__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	0.55 kW	932 r/min	0.96 A	0.650	65.80 %	5.61 N·m	4.70
D	--	50 Hz	400 V	0.55 kW	932 r/min	1.67 A	0.650	65.80 %	5.61 N·m	4.70
Y	--	50 Hz	660 V	0.55 kW	922 r/min	0.91 A	0.730	65.80 %	5.67 N·m	4.70
D	--	50 Hz	380 V	0.55 kW	922 r/min	1.58 A	0.730	65.80 %	5.67 N·m	4.70
D	--	60 Hz	440 V	0.55 kW	1136 r/min	1.40 A	0.680	66.00 %	4.60 N·m	5.60
D	--	60 Hz	460 V	0.55 kW	1142 r/min	1.52 A	0.610	66.00 %	4.58 N·m	5.40

Temperature Class	--
Default	
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 65.8 % Partial Load (75%) 63.2 % Partial Load (50%) 57.3 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 66.0 % Partial Load (75%) 61.5 % Partial Load (50%) 54.0 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Cast Iron
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	19 kg
Gross Weight	22 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE1 Standard Efficiency Cast Iron Motors

