

PRODUCT-DETAILS

3GBA083410-ASD

IE3 Premium Efficiency Cast Iron Motors, 0.55 kW, 400 V (3GBA083410-ASD)



General Information	
Product ID	3GBA083410-ASD
ABB Type Designation	M2BAX 80MLA 6
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 0.55 kW, 400 V (3GBA083410-ASD)

Ordering	
ABB Type Designation	M2BAX 80MLA 6
Invoice Description	M2BAX 80MLA 6
Product Name	3-Phase squirrel cage motor
Product Type	EBA3__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Menden, Germany Shanghai, China
Medium Description	0.55kW, 6 Poles, Frame Size 80, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GBA083410-ASD)
Short Description	0.55kW, 6P, Frame Size 80, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.55 kW	943 r/min	1.54 A	0.680	77.20 %	5.60 N·m	6.30
D	--	50 Hz	230 V	0.55 kW	943 r/min	2.68 A	0.680	77.20 %	5.60 N·m	6.30
Y	--	50 Hz	380 V	0.55 kW	934 r/min	1.54 A	0.710	77.20 %	5.61 N·m	5.90
D	--	50 Hz	220 V	0.55 kW	934 r/min	2.67 A	0.710	77.20 %	5.61 N·m	5.90
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										0.55 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 77.2 % Partial Load (75%) 75.9 % Partial Load (50%) 71.8 %
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 68.0 % Partial Load (75%) 64.5 % Partial Load (50%) 57.0 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Cast Iron
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	334 mm
Product Net Height	192 mm
Product Net Width	154 mm
Product Net Weight	23 kg
Gross Weight	26 kg

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

