




PRODUCT-DETAILS

3GBA091510-BEC

IE2 High Efficiency Cast Iron Motors, 2.2 kW,
500 V (3GBA091510-BEC)



General Information

Product ID	3GBA091510-BEC
ABB Type Designation	M2BAX 90LA 2
Catalog Description	IE2 High Efficiency Cast Iron Motors, 2.2 kW, 500 V (3GBA091510-BEC)

Ordering

ABB Type Designation	M2BAX 90LA 2
Invoice Description	M2BAX 90LA 2
Product Name	3-Phase squirrel cage motor
Product Type	EBA2_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Poland (PL)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Shanghai, China
Medium Description	2.2kW, 2 Poles, Frame Size 90, 3 Phases, 500V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GBA091510-BEC)
Short Description	2.2kW, 2P, Frame Size 90, 3PH, 500V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	500 V	2.20 kW	2883 r/min	3.49 A	0.870	83.20 %	7.28 N·m	7.20
D	--	60 Hz	575 V	2.20 kW	3496 r/min	2.94 A	0.890	81.50 %	6.00 N·m	8.90
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U _{in})										500 V
Frequency (f)										50 Hz
Output Power										2.2 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 83.2 % Partial Load (75%) 83.5 % Partial Load (50%) 82.7 %
IE Class Data (60 Hz)										IE Class IE1 Full Load (100%) 81.5 % Partial Load (75%) 80.6 % Partial Load (50%) 78.0 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										E

Mechanical

Frame Material	Cast Iron
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	351 mm
Product Net Height	217 mm
Product Net Width	195 mm
Product Net Weight	24 kg
Gross Weight	27 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

