



PRODUCT-DETAILS

3GBA091213-HFB

No Description Available

General Information																																												
Product ID								3GBA091213-HFB																																				
ABB Type Designation								M2BA 90SLC 2																																				
Catalog Description								No Description Available																																				
Additional Information																																												
ABB Type Designation								M2BA 90SLC 2																																				
Altitude								1000 m																																				
Ambient Temperature								40 °C																																				
Bearing								6205-2Z/C3																																				
Bearing NDE								6204-2Z/C3																																				
Country of Origin								India (IN) China (CN)																																				
Customs Tariff Number								85015220																																				
Direction of Rotation								Both sides																																				
Electrical Data																																												
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th><th>Efficiency</th><th>Torque</th><th>IS/IN</th></tr><tr><td>Y</td><td>--</td><td>50 Hz</td><td>500 V</td><td>2.20 kW</td><td>2885 r/min</td><td>3.40 A</td><td>0.870</td><td>84.70 %</td><td>7.20 N·m</td><td>6.80</td></tr><tr><td>Y</td><td>--</td><td>60 Hz</td><td>575 V</td><td>2.20 kW</td><td>3500 r/min</td><td>2.80 A</td><td>0.880</td><td>86.40 %</td><td>6.00 N·m</td><td>7.90</td></tr></table>												Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	Y	--	50 Hz	500 V	2.20 kW	2885 r/min	3.40 A	0.870	84.70 %	7.20 N·m	6.80	Y	--	60 Hz	575 V	2.20 kW	3500 r/min	2.80 A	0.880	86.40 %	6.00 N·m	7.90
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN																																		
Y	--	50 Hz	500 V	2.20 kW	2885 r/min	3.40 A	0.870	84.70 %	7.20 N·m	6.80																																		
Y	--	60 Hz	575 V	2.20 kW	3500 r/min	2.80 A	0.880	86.40 %	6.00 N·m	7.90																																		
Frame Size								90																																				
Gross Weight								26 kg																																				
IC Class								IC411																																				
IE Class Data (50 Hz)								IE Class IE2 Full Load (100%) 84.7 % Partial Load (75%) 86.7 % Partial Load (50%) 85.7 %																																				
IE Class Data (60 Hz)								IE Class IE2 Full Load (100%) 86.4 %																																				
IM Class								IMB35 IM2001																																				
Insulation Class								ICLF																																				
IP Class								IP55																																				
Lubrication								For life																																				
Made To Order								No																																				
Minimum Order Quantity								1 piece																																				
Number of Poles (High)								2																																				
Package Level 1 Units								0 carton																																				
Pre Modified Motor								3GBA091213-AFB																																				
Product ID																																												

Product Name	3-Phase squirrel cage motor
Product Net Weight	25 kg
Product Type	2BA2_M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	F
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)