



PRODUCT-DETAILS

3GBA092110-ASCCNCB
M2BAX 90SA4

General Information	
Product ID	3GBA092110-ASCCNCB
ABB Type Designation	M2BAX 90SA 4
Catalog Description	M2BAX 90SA4

Additional Information	
ABB Type Designation	M2BAX 90SA 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	380 V	1.10 kW	1440 r/min	2.67 A	0.770	81.40 %	7.35 N·m	6.30
D	--	50 Hz	220 V	1.10 kW	1440 r/min	4.61 A	0.770	81.40 %	7.35 N·m	6.30
Y	--	50 Hz	400 V	1.10 kW	1445 r/min	2.67 A	0.730	81.40 %	7.35 N·m	6.60

Frame Size	90
Gross Weight	21 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2
	Full Load (100%) 81.4 %
	Partial Load (75%) 79.5 %
	Partial Load (50%) 75.7 %
IM Class	IMB34 IM2101
Insulation Class	ICLF
Invoice Description	M2BAX 90SA4
IP Class	IP55
Lubrication	For life
Made To Order	No

Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	21 kg
Product Type	CBA2__M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Temperature Rise	80 K
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)