


PRODUCT-DETAILS

3GBA092120-BDD

IE3 Premium Efficiency Cast Iron Motors, 1.1 kW, 400 V (3GBA092120-BDD)



General Information

Product ID	3GBA092120-BDD
ABB Type Designation	M2BAX 90SB 4
Catalog Description	IE3 Premium Efficiency Cast Iron Motors, 1.1 kW, 400 V (3GBA092120-BDD)

Ordering

ABB Type Designation	M2BAX 90SB 4
Invoice Description	M2BAX 90SB 4
Product Name	3-Phase squirrel cage motor
Product Type	EBA3_M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany Shanghai, China
Medium Description	1.1kW, 4 Poles, Frame Size 90, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GBA092120-BDD)
Short Description	1.1kW, 4P, Frame Size 90, 3PH, 400V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	1.10 kW	1433 r/min	1.48 A	0.730	84.10 %	7.33 N·m	7.10
D	--	50 Hz	400 V	1.10 kW	1433 r/min	2.55 A	0.730	84.10 %	7.33 N·m	7.10
Y	--	50 Hz	660 V	1.10 kW	1426 r/min	1.49 A	0.770	84.10 %	7.37 N·m	6.50
D	--	50 Hz	380 V	1.10 kW	1426 r/min	2.58 A	0.770	84.10 %	7.37 N·m	6.50

Connection Configuration	D
Temperature Class	--
Default	
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	1.1 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 84.1 % Partial Load (75%) 84.1 % Partial Load (50%) 81.7 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 84.0 % Partial Load (75%) 82.2 % Partial Load (50%) 78.9 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	D

Mechanical

Frame Material	Cast Iron
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	335 mm
Product Net Height	217 mm
Product Net Width	170 mm
Product Net Weight	23 kg
Gross Weight	26 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications	
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

