



PRODUCT-DETAILS

# 3GBA092212-BDB

## No Description Available

General Information																																																							
Product ID								3GBA092212-BDB																																															
ABB Type Designation								M2BA 90SLB 4																																															
Catalog Description								No Description Available																																															
Additional Information																																																							
ABB Type Designation								M2BA 90SLB 4																																															
Altitude								1000 m																																															
Ambient Temperature								40 °C																																															
Bearing								6205-2Z/C3																																															
Bearing NDE								6203-2Z/C3																																															
Country of Origin								India (IN) China (CN) Poland (PL)																																															
Customs Tariff Number								85015220																																															
Electrical Data																																																							
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th><th>Efficiency</th><th>Torque</th><th>IS/IN</th></tr><tr><td>Y</td><td>--</td><td>50 Hz</td><td>690 V</td><td>1.10 kW</td><td>1435 r/min</td><td>1.37 A</td><td>0.800</td><td>81.40 %</td><td>7.30 N·m</td><td>6.50</td></tr><tr><td>D</td><td>--</td><td>50 Hz</td><td>400 V</td><td>1.10 kW</td><td>1435 r/min</td><td>2.36 A</td><td>0.800</td><td>81.40 %</td><td>7.30 N·m</td><td>6.50</td></tr><tr><td>D</td><td>--</td><td>60 Hz</td><td>460 V</td><td>1.10 kW</td><td>1740 r/min</td><td>2.11 A</td><td>0.770</td><td>84.00 %</td><td>6.00 N·m</td><td>7.50</td></tr></table>												Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	Y	--	50 Hz	690 V	1.10 kW	1435 r/min	1.37 A	0.800	81.40 %	7.30 N·m	6.50	D	--	50 Hz	400 V	1.10 kW	1435 r/min	2.36 A	0.800	81.40 %	7.30 N·m	6.50	D	--	60 Hz	460 V	1.10 kW	1740 r/min	2.11 A	0.770	84.00 %	6.00 N·m	7.50
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN																																													
Y	--	50 Hz	690 V	1.10 kW	1435 r/min	1.37 A	0.800	81.40 %	7.30 N·m	6.50																																													
D	--	50 Hz	400 V	1.10 kW	1435 r/min	2.36 A	0.800	81.40 %	7.30 N·m	6.50																																													
D	--	60 Hz	460 V	1.10 kW	1740 r/min	2.11 A	0.770	84.00 %	6.00 N·m	7.50																																													
Frame Size								90																																															
Gross Weight								28 kg																																															
IC Class								IC411																																															
IE Class Data (50 Hz)								IE Class IE2 Full Load (100%) 81.4 % Partial Load (75%) 82.0 % Partial Load (50%) 80.1 %																																															
IE Class Data (60 Hz)								IE Class IE2 Full Load (100%) 84.0 % Partial Load (75%) 83.6 % Partial Load (50%) 81.0 %																																															
IM Class								IMB5 IM3001																																															
Insulation Class								ICLF																																															
IP Class								IP55																																															
Lubrication								For life																																															
Made To Order								No																																															
Minimum Order Quantity								1 piece																																															
Number of Poles (High)								4																																															

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	25 kg
Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class	--
Default	
Terminator Box Location	Top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)