



PRODUCT-DETAILS

3GBA092215-CSB

No Description Available

"No longer for sale" replaced by 3GBA092510-

General Information											
Product ID						3GBA092215-CSB					
ABB Type Designation						M2BA 90SLD 4					
Catalog Description						No Description Available					
Additional Information											
ABB Type Designation						M2BA 90SLD 4					
Altitude						1000 m					
Ambient Temperature						40 °C					
Bearing						6205-2Z/C3					
Bearing NDE						6204-2Z/C3					
Country of Origin						India (IN) China (CN)					
Customs Tariff Number						85015220					
Direction of Rotation						Both sides					
Electrical Data											
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	
Y	--	50 Hz	400 V	1.50 kW	1430 r/min	3.00 A	0.830	84.30 %	10.00 N·m	6.30	
D	--	50 Hz	230 V	1.50 kW	1430 r/min	5.10 A	0.830	84.30 %	10.00 N·m	6.30	
Y	--	60 Hz	460 V	1.50 kW	1740 r/min	2.70 A	0.800	86.10 %	8.20 N·m	7.20	
Frame Material						Cast Iron					
Frame Size						90					
Gross Weight						28 kg					
IC Class						IC411					
IE Class Data (50 Hz)						IE Class IE2 Full Load (100%) 84.3 % Partial Load (75%) 85.6 % Partial Load (50%) 84.7 %					
IE Class Data (60 Hz)						IE Class IE2 Full Load (100%) 86.1 %					
IM Class						IMB14 IM3601					
Insulation Class						ICLF					

IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	27 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Replacement Product ID (NEW)	3GBA092510-CSC
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)