

PRODUCT-DETAILS

3GBA093010-ASNCN

IE4 Super Premium Efficiency Cast Iron Motors, 0,75 kW, 400 V (3GBA093010-ASNCN)



General Information	
Product ID	3GBA093010-ASNCN
ABB Type Designation	M2BAX 90SLA 6
Catalog Description	IE4 Super Premium Efficiency Cast Iron Motors, 0,75 kW, 400 V (3GBA093010-ASNCN)

Ordering	
ABB Type Designation	M2BAX 90SLA 6
Invoice Description	M2BAX 90SLA 6
Product Name	3-Phase squirrel cage motor
Product Type	CBA4__M2BAX_IE4_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Medium Description	0.75kW, 6 Poles, Frame Size 90, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB3/IM1001 Mounting (3GBA093010-ASNCN)
Short Description	0.75kW, 6P, Frame Size 90, 3PH, 400V, 50Hz, IP55, IMB3/IM1001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	0.75 kW	948 r/min	1.82 A	0.720	82.70 %	7.55 N·m	4.90
D	--	50 Hz	230 V	0.75 kW	948 r/min	3.16 A	0.720	82.70 %	7.55 N·m	4.90
Y	--	50 Hz	380 V	0.75 kW	941 r/min	1.84 A	0.750	82.70 %	7.60 N·m	4.60
D	--	50 Hz	220 V	0.75 kW	941 r/min	3.17 A	0.750	82.70 %	7.60 N·m	4.60
Y	--	60 Hz	440 V	0.75 kW	1149 r/min	1.65 A	0.710	84.00 %	6.23 N·m	5.30
Y	--	60 Hz	460 V	0.75 kW	1154 r/min	1.65 A	0.680	84.00 %	6.20 N·m	5.60

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	0,75 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 82.7 % Partial Load (75%) 82.7 % Partial Load (50%) 81.3 %
IE Class Data (60 Hz)	IE Class IE4 Full Load (100%) 84.0 % Partial Load (75%) 83.0 % Partial Load (50%) 80.8 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Cast Iron
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	351 mm
Product Net Height	217 mm
Product Net Width	170 mm

Product Net Weight	29 kg
Gross Weight	32 kg

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE4 Super Premium Efficiency Cast Iron Motors

