



PRODUCT-DETAILS

3GBA093213-ADB

No Description Available

General Information	
Product ID	3GBA093213-ADB
ABB Type Designation	M2BA 90SLC 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 90SLC 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015100
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	690 V	0.75 kW	960 r/min	1.37 A	0.580	76.30 %	7.40 N·m	4.50
D	--	50 Hz	400 V	0.75 kW	960 r/min	2.30 A	0.580	76.30 %	7.40 N·m	4.50
D	--	60 Hz	460 V	0.75 kW	1160 r/min	2.10 A	0.540	80.40 %	6.10 N·m	5.10

Frame Size	90
Gross Weight	28 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 76.3 % Partial Load (75%) 74.7 % Partial Load (50%) 69.4 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 80.4 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece

Number of Poles (High)	6
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	25 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	Top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)