



PRODUCT-DETAILS

3GBA093214-ASB

No Description Available

General Information

Product ID	3GBA093214-ASB
ABB Type Designation	M2BA 90SLE 6
Catalog Description	No Description Available

Additional Information

ABB Type Designation	M2BA 90SLE 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	India (IN) China (CN) Poland (PL)
Customs Tariff Number	85015220

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.10 kW	930 r/min	3.00 A	0.660	78.20 %	11.20 N·m	4.00
D	--	50 Hz	230 V	1.10 kW	930 r/min	5.22 A	0.660	78.20 %	11.20 N·m	4.00
Y	--	60 Hz	460 V	1.10 kW	1140 r/min	2.60 A	0.650	81.20 %	9.20 N·m	4.60

Frame Size	90
Gross Weight	31 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 78.2 % Partial Load (75%) 78.6 % Partial Load (50%) 76.4 %
IE Class Data (60 Hz)	IE Class IE1 Full Load (100%) 81.2 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor

Product Net Weight	28 kg
Product Type	2BA2_M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Terminator Box Location	Top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)