



PRODUCT-DETAILS

3GBA093213-ASBCN

No Description Available

General Information	
Product ID	3GBA093213-ASBCN
ABB Type Designation	M2BA 90SLC 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 90SLC 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	0.75 kW	960 r/min	3.90 A	0.620	79.80 %	7.40 N·m	4.40
Y	--	50 Hz	380 V	0.75 kW	960 r/min	2.30 A	0.620	79.80 %	7.40 N·m	4.40
D	--	50 Hz	230 V	0.75 kW	960 r/min	3.90 A	0.580	78.70 %	7.40 N·m	4.50
Frame Size										
										90
Gross Weight										25 kg
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2
										Full Load (100%) 78.7 %
										Partial Load (75%) 77.3 %
										Partial Load (50%) 72.5 %
IE Class Data (60 Hz)										IE Class IE2
										Full Load (100%) 80.4 %
IM Class										IMB3 IM1001
Insulation Class										ICLF
IP Class										IP55
Lubrication										For life
Made To Order										No
Minimum Order Quantity										1 piece

Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	25 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)