



PRODUCT-DETAILS

3GBA093443-AHB

No Description Available

General Information	
Product ID	3GBA093443-AHB
ABB Type Designation	M2BA 90SLC 6
EAN	3GBA093443-AHB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 90SLC 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
Country of Origin	Spain (ES) India (IN) China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
EAN	3GBA093443-AHB
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	415 V	0.75 kW	960 r/min	2.40 A	0.550

Frame Size	90
Gross Weight	26 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 77.5 % Partial Load (75%) 75.2 % Partial Load (50%) 69.7 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	25 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)