



PRODUCT-DETAILS

3GBA093510-ASCCN  
(3GBA093510-ASCCN)



General Information	
Product ID	3GBA093510-ASCCN
ABB Type Designation	M2BAX 90LA 6
Catalog Description	(3GBA093510-ASCCN)

Ordering	
ABB Type Designation	M2BAX 90LA 6
Invoice Description	M2BAX 90LA 6
Product Name	3-Phase squirrel cage motor
Product Type	CBA2__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015100
Stocked At (Warehouses)	Shanghai, China Guangzhou, China China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.10 kW	936 r/min	3.17 A	0.650	78.10 %	11.06 N-m	4.60
D	--	50 Hz	230 V	1.10 kW	936 r/min	5.49 A	0.650	78.10 %	11.06 N-m	4.60
Y	--	50 Hz	380 V	1.10 kW	926 r/min	3.14 A	0.690	78.10 %	11.10 N-m	4.40
D	--	50 Hz	220 V	1.10 kW	926 r/min	5.44 A	0.700	78.10 %	11.10 N-m	4.40
Y	--	60 Hz	440 V	1.10 kW	1137 r/min	2.82 A	0.650	75.00 %	9.22 N-m	5.10
Y	--	60 Hz	460 V	1.10 kW	1143 r/min	2.86 A	0.610	75.00 %	9.18 N-m	5.30
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 78.1 % Partial Load (75%) 76.2 % Partial Load (50%) 72.7 %
IE Class Data (60 Hz)										IE Class IE1 Full Load (100%) 75.0 % Partial Load (75%) 71.5 % Partial Load (50%) 65.9 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Cast Iron
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6205-2Z/C3
Lubrication	For life
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	25 kg
Gross Weight	28 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications	
Standards	IEC 60034-1
UNSPSC	26101100

Categories
Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

