



PRODUCT-DETAILS

3GBA101212-CFB

No Description Available

General Information																																												
Product ID								3GBA101212-CFB																																				
ABB Type Designation								M2BA 100LB 2																																				
Catalog Description								No Description Available																																				
Additional Information																																												
ABB Type Designation								M2BA 100LB 2																																				
Altitude								1000 m																																				
Ambient Temperature								40 °C																																				
Bearing								6206-2Z/C3																																				
Bearing NDE								6205-2Z/C3																																				
Country of Origin								India (IN) China (CN)																																				
Customs Tariff Number								85015220																																				
Direction of Rotation								Both sides																																				
Electrical Data																																												
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th><th>Efficiency</th><th>Torque</th><th>IS/IN</th></tr><tr><td>Y</td><td>--</td><td>50 Hz</td><td>500 V</td><td>3.00 kW</td><td>2925 r/min</td><td>4.70 A</td><td>0.860</td><td>85.20 %</td><td>9.70 N·m</td><td>9.10</td></tr><tr><td>Y</td><td>--</td><td>60 Hz</td><td>575 V</td><td>3.00 kW</td><td>3530 r/min</td><td>3.90 A</td><td>0.870</td><td>87.50 %</td><td>8.10 N·m</td><td>10.50</td></tr></table>												Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN	Y	--	50 Hz	500 V	3.00 kW	2925 r/min	4.70 A	0.860	85.20 %	9.70 N·m	9.10	Y	--	60 Hz	575 V	3.00 kW	3530 r/min	3.90 A	0.870	87.50 %	8.10 N·m	10.50
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN																																		
Y	--	50 Hz	500 V	3.00 kW	2925 r/min	4.70 A	0.860	85.20 %	9.70 N·m	9.10																																		
Y	--	60 Hz	575 V	3.00 kW	3530 r/min	3.90 A	0.870	87.50 %	8.10 N·m	10.50																																		
Frame Size								100																																				
Gross Weight								37 kg																																				
IC Class								IC411																																				
IE Class Data (50 Hz)								IE Class IE2 Full Load (100%) 85.2 % Partial Load (75%) 84.9 % Partial Load (50%) 82.8 %																																				
IE Class Data (60 Hz)								IE Class IE2 Full Load (100%) 87.5 %																																				
IM Class								IMB14 IM3601																																				
Insulation Class								ICLF																																				
IP Class								IP55																																				
Lubrication								For life																																				
Made To Order								No																																				

Minimum Order Quantity	1 piece
Number of Poles (High)	2
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	36 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	F
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)